

MODEL COMPARISON CHART

MODEL N O .		ELECTRIC BIDET			FAR INFRARED RAY BIDET	
		 PB-X5500	 PB-X2500	 PB-X800	 XB-U5700	 XB-U3000B
CLEANSING	NOZZLE	TWIN	TWIN	TWIN	TWIN	TWIN
	FAR INFRARED RAY NOZZLE	-	-	-	✓	✓
	STAINLESS NOZZLE	optional	optional	optional	optional	optional
	WARM WATER	✓	✓	✓	✓	✓
	ANTERIOR/ FEMININE	✓	✓	✓	✓	✓
	POSTERIOR/ FAMILY	✓	✓	✓	✓	✓
	SELF CLEAN	✓	✓	✓	✓	✓
	ENEMA / MASSAGE	✓	✓	-	✓	✓
	WIDE WASH	-	-	-	✓	-
CONTROL	CHILD WASH	✓	-	-	✓	-
	SEAT TEMPERATURE	✓	✓	✓	✓	✓
	WATER TEMPERATURE	✓	✓	✓	✓	✓
	WARM AIR TEMPERATURE	✓	✓	Optional	✓	✓
	WATER PRESSURE	✓	✓	✓	✓	✓
SAFETY	NOZZLE POSITION	✓	✓	✓	✓	✓
	ELECTRIC CIRCUIT BREAKER	optional	optional	optional	optional	optional
	SEAT SENSOR	✓	✓	Optional	✓	✓
CONVENIENT	ANTI-BACTERIAL	✓	✓	✓	✓	✓
	WIRELESS REMOTE	-	-	-	-	-
	CONTROL PANEL	✓	✓	✓	✓	✓
	ENERGY SAVING	✓	✓	-	✓	✓
SANITATION	SOFT CLOSE	✓	✓	✓	✓	✓
	DEODORIZER	✓	✓	-	✓	✓
COLOR	WATER PURIFIER	✓	✓	-	✓	✓
	WHITE & RED	✓			✓	✓
	WHITE & BLACK	✓			✓	
Others	WHITE		✓	✓		✓
	N/W, G/W	5kg / 7 kg	5kg / 7 kg	5kg / 7 kg	5kg / 7 kg	5kg / 7 kg
	Dim. (W x L x H)	476 x 535 x 150	483 x 530 x 137	483 x 530 x 137	476 x 535 x 150	483 x 530 x 137
	Packing (W x L x H)	588 x 542 x 202	602 x 542 x 202	602 x 542 x 202	588 x 542 x 202	602 x 542 x 202



High technological functions will upgrade quality of your life.



FAR INFRARED RAY SAFE STERILIZATION

Features of Far-Infrared Ray Nozzle



Effect of Far Infrared ray

Has the ability to penetrate, refract, radiate & reflect. The human body can absorb FIR because of its deep penetrating ability. When FIR penetrates through the skin to the subcutaneous tissues, it transforms from light energy into heat energy.

The thermal effect within the deep layers of tissues cause blood vessels in capillaries to dilate, promoting better blood circulation, and the heat produced helps to get rid of body toxins and metabolic wastes through sweating.

Why Far-Infrared Ray Nozzle?

- Bacteria on Nozzle tip of wash / bidet to be sterilized by 99.9% by Far Infrared Ray Heater for cleaning & securing washing of nozzle.
- The nozzle with Far Infrared Ray enable to promote metabolic by Far Infrared ray during use of Bidet.

How To Operate?

1. When seated Far-Infrared rays heater begins to work to sterilize nozzle tip.
2. When wash/bidet is operated, Far-Infrared rays come in contact with body improves human health system
3. After wash/bidet is operated, as self nozzle cleaning process, Far-Infrared rays sterilize nozzle tip for 10 minutes.

Test results of Far Infrared ray's sterilization



Tested by	Type of Bacteria				
	E. Coli	Stacpch uysloco	S. typhimurium	S. flexneri	P. aeruginosa
KRICT Reg.no.: 20069-TBH-000565	-	-	99.9%	86.7%	94%
KIDA Reg.no.: KFA-140	99.9%	99.9%	-	-	-

Test results of Far Infrared ray

Tested by	Emissivity(5~20um)	Radiation Energy (W/m2.um, 150°C)
KIDA Reg.no.: KFA-140	Tested by	Tested by

PASECO Bidet aims to make **99.9% sterilizable** antibacterial bidet for clean & healthy use by Far-Infrared ray, anti-bacterial nozzle, anti-bacterial seat that PASECO's cutting-edge technology enable perfect sterilization system.

PATENT FAR INFRARED RAY BIDET

XB-U5700

- Far Infrared Ray Nozzle
- Energy Saving
- Powerful Deodorizer (Carbon Filter)
- Warm Water / Warm Air Dryer
- Adjustable Seat/water temp
- Adjustable water pressure
- Enema / Massage Wash
- Auto Wash / Child Wash
- Water Purifier / Seat Sensor



XB-U3000

- Far Infrared Ray Nozzle
- Energy Saving
- Warm Water / Warm Air Dryer
- Powerful Deodorizer (Carbon Filter)
- Adjustable Seat/water temp
- Adjustable water pressure
- Massage Was / Auto Wash
- Seat Sensor / Water Purifier



FAR INFRARED RAY STERILIZATION
Killing 99.9% of bacteria from nozzle



POWERFUL DEODORIZER



HOT WATER NOZZLE STERILIZATION
Additional for perfect killing bacteria



SEAT SENSOR



POWER SAVING



WATER PURIFIER

ELECTRIC BIDET

PB-X5500



- Energy Saving
- Warm Water / Warm Air Dryer
- Powerful Deodorizer (Carbon Filter)
- Adjustable Seat/water temp
- Adjustable water pressure
- Enema / Massage Wash
- Auto Wash / Child Wash
- Seat Sensor / Water Purifier
- Optional
 - Stainless Nozzle
 - Electric Circuit Breaker

PB-X2500



- Energy Saving
- Warm Water / Warm Air Dryer
- Powerful Deodorizer (Carbon Filter)
- Adjustable Seat/water temp
- Adjustable water pressure
- Massage / Auto Wash
- Seat Sensor / Water Purifier
- Optional
 - Stainless Nozzle
 - Electric Circuit Breaker

PB-X800



- Warm Water
- Adjustable Seat/water temp
- Adjustable water pressure
- Optional
 - Stainless Nozzle
 - Warm Air Dryer
 - Seat Sensor




NOZZLE SELF-CLEANING
Warm water washing during 1 min after use to clean nozzles



SOFT CLOSE
Prevent seat cover damage



POWER SAVING



WIDE WASH



TWIN NOZZLE



REMOTE CONTROLLER



HEATED SEAT



ADJUSTABLE NOZZLE POSITION